



NOTES:
 1. SPECIFICATIONS
 Current Rating: 1A AC,DC
 Voltage Rating: 125V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 500V AC/minute
 2. Material & finish:
 Housing: Natural Thermoplastic, UL94V-0
 Contact and metal hold-down: Phosphor Bronze
 Plating of contact: Matte Tin or gold on contact area, 100u"Min. Matte Tin on tail, 50u"Min. Ni overall as underplating
 Plating of metal hold-down: 100u"Min. Matte Tin overall, 50u"Min. Nickel overall as underplating
 3. Crimping application hand tool P/N: 10118656-1000
 4. Ordering Information & Dimensions:
 10114830- X X X XX LF
 Material: 1: LCP Natural Non Glow Wire Compatible; 2: LCP Natural Glow Wire Compatible; 3: LCP Black Glow Wire Compatible
 LF: See note A; Pin counts from 02~15
 Packaging: 1: Tape & Reel; 2: ESD Tape & Reel
 Plating on contact: 0: Matte Tin 100u"; 1: Gold Flash; 2: Gold 15u"; 3: Gold 30u"

PART NO.	Dimensions			
	A	B	C	D
10114830-xxx02LF	4.25	1.25±0.10	4.94	3.05
10114830-xxx03LF	5.50	2.50±0.10	6.19	4.30
10114830-xxx04LF	6.75	3.75±0.15	7.44	5.55
10114830-xxx05LF	8.00	5.00±0.10	8.69	6.80
10114830-xxx06LF	9.25	6.25±0.15	9.94	8.05
10114830-xxx07LF	10.50	7.50±0.15	11.19	9.30
10114830-xxx08LF	11.75	8.75±0.15	12.44	10.55
10114830-xxx09LF	13.00	10.00±0.15	13.69	11.80
10114830-xxx10LF	14.25	11.25±0.20	14.94	13.05
10114830-xxx11LF	15.50	12.50±0.20	16.19	14.30
10114830-xxx12LF	16.75	13.75±0.20	17.44	15.55
10114830-xxx13LF	18.00	15.00±0.20	18.69	16.80
10114830-xxx14LF	19.25	16.25±0.20	19.94	18.05
10114830-xxx15LF	20.50	17.50±0.20	21.19	19.30

Note A: The LF means RoHS compliance, the housing will withstand exposure to peak temperature 260 degree C for 5 sec in the IR re-flow process.

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO		projection 1101		product family WTB	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm		title	
A	T10-0145	JH	12/1/10	angles	.0±.25	← mm →		WTB 1.25MM WAFER 90° SMT	
F	ELX-N-20168	TIM	02/03/15	linear	.00±.15	scale 1:1		dwg no	
G	ELX-N-21788	TIM	08/27/15	0'±2'	.000±			sheet 1 of 1	
H	ELX-N-27088	TONY	05/24/17	dr	JASON HSU	12/1/10		size	
J	ELX-N-27325	TONY	06/26/17	engr	JASON HSU	12/1/10		10114830	
K	ELX-N-29884	TONY	04/17/17	chr	GARY HSIEH	12/1/10		A3	
L	ELX-N-30309	TONY	05/28/18	app	JOSEPH HSIA	12/1/10		type Product Customer Drawing	
sheet	revision	L							
index	sheet	1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10114830-10102LF](#) [10114830-10103LF](#) [10114830-10104LF](#) [10114830-10105LF](#) [10114830-10106LF](#) [10114830-10107LF](#) [10114830-10108LF](#) [10114830-10109LF](#) [10114830-10110LF](#) [10114830-10111LF](#) [10114830-10112LF](#) [10114830-10113LF](#) [10114830-10114LF](#) [10114830-10115LF](#) [10114830-11102LF](#) [10114830-11103LF](#) [10114830-11104LF](#) [10114830-11105LF](#) [10114830-11106LF](#) [10114830-11107LF](#) [10114830-11108LF](#) [10114830-11109LF](#) [10114830-11110LF](#) [10114830-11111LF](#) [10114830-11112LF](#) [10114830-11113LF](#) [10114830-11114LF](#) [10114830-11115LF](#) [10114830-13104LF](#) [10114830-13102LF](#) [10114830-13106LF](#) [10114830-13105LF](#) [10114830-13103LF](#) [10114830-13108LF](#) [10114830-13110LF](#) [10114830-12102LF](#) [10114830-12104LF](#) [10114830-20110LF](#) [10114830-21104LF](#) [10114830-21103LF](#) [10114830-21102LF](#) [10114830-13115LF](#) [10114830-20107LF](#) [10114830-21112LF](#) [10114830-21108LF](#) [10114830-21106LF](#)