



C13U18 (USA)

Country of Origin: China
 Manufacturer: SUNNY
 Operating Temperature: 0 ÷ 40[°C]
 Length/cord : 1.8m / 3x0,824 mm2
 Approvals : UL, CSA



| | | |
|---------------------|-------------------------|------------------------|
| Application | For Class I. Appliances | |
| USA Plug | NEMA 5-15 (B) 10A/125V | |
| C13 Plug | 10A/125V | |
| Cable construction | 18AWG SVT | |
| Max current | 10A | |
| Insulation material | PVC | |
| Rated voltage | 300V 105°C | |
| WEIGHT / PACKING | 1pc | N.W.: 149g / pc |
| | Box | 0.55 x 0.36 x 0.20 [m] |
| | | 125 pcs / 1box |
| | | G.W.: 20.15kg / box |