



# M28840/24 Mounting Gasket



MIL-DTL  
28840



| Designator | A             | B Dia.        | C             | D Dia.                     |
|------------|---------------|---------------|---------------|----------------------------|
| A (11)     | .760 (19.30)  | .766 (19.46)  | 1.039 (26.39) | .130 (3.30)<br>.110 (2.79) |
|            | .740 (18.80)  | .750 (19.05)  | 1.023 (25.98) |                            |
| B (13)     | .853 (21.67)  | .891 (22.63)  | 1.154 (29.31) |                            |
|            | .833 (21.16)  | .875 (22.22)  | 1.138 (28.90) |                            |
| C (15)     | .978 (24.84)  | 1.078 (27.38) | 1.274 (32.36) |                            |
|            | .958 (24.33)  | 1.062 (26.97) | 1.258 (31.95) |                            |
| D (17)     | 1.025 (26.04) | 1.141 (28.98) | 1.399 (26.39) |                            |
|            | 1.005 (25.53) | 1.125 (28.58) | 1.383 (35.13) |                            |
| E (19)     | 1.150 (29.21) | 1.338 (33.98) | 1.524 (38.71) |                            |
|            | 1.130 (28.70) | 1.312 (33.32) | 1.508 (38.30) |                            |
| F (23)     | 1.291 (32.79) | 1.516 (38.51) | 1.734 (44.04) |                            |
|            | 1.271 (32.28) | 1.500 (38.10) | 1.718 (43.64) |                            |
| G (25)     | 1.402 (35.61) | 1.641 (41.68) | 1.834 (46.58) | .157 (3.99)<br>.137 (3.48) |
|            | 1.382 (35.10) | 1.625 (41.28) | 1.818 (46.18) |                            |
| H (29)     | 1.578 (40.08) | 1.891 (48.03) | 2.154 (54.71) |                            |
|            | 1.558 (39.57) | 1.875 (47.62) | 2.138 (54.30) |                            |
| J (33)     | 1.744 (44.30) | 2.078 (52.78) | 2.344 (59.54) | .183 (4.65)<br>.163 (4.14) |
|            | 1.724 (43.79) | 2.062 (52.37) | 2.328 (59.13) |                            |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[M28840/1CW](#) [M28840/1GW](#) [M28840/1DW](#) [M28840/1EW](#) [M28840/1FW](#) [M28840/1JW](#) [M28840/1BW](#)  
[M28840/24AA](#) [M28840/1AW](#) [M28840/24AB](#) [M28840/24BB](#)