

Specification Sheet

Part Number: 110-80004



Tensions and provides clean, flush cuts for 50lb. to 250lb. cable ties, including wide strap ties.

Impact-resistant housing and durable components for extended service life.

Easy-to-adjust tension knob offers 33 different settings for precise, repeatable applications.

Advanced ergonomic design minimizes necessary hand force and “kickback” to reduce repetitive-motion injuries.

EVO 9HT High Tension Mechanical Hand Tool, Tension Range 27 lb to 116 lb, 1/pkg

Article Number 110-80004

Type EVO9HT

Color Black (BK) Red (RD)

Product Description HellermannTyton's EVO 9 manual cable tie application tool combines durability, precision and control with unparalleled comfort. Manufactured with high-performance materials and components, the EVO 9 cuts cable ties with up to 250-lb tensile strength. Its innovative, ergonomic design minimizes the stress on hands and wrists and “kickback” that occur with traditional tools, reducing the risk of repetitive-motion injuries. The HT model offers high tension while the SP model features a smaller grip.

Short Description	EVO 9HT High Tension Mechanical Hand Tool, Tension Range 27 lb to 116 lb, 1/pkg
Global Part Name	EVO9HT-MET/PL-BK/RD
Technical Description	Tension Range 27 lb to 116 lb
Length L (Imperial)	7.5
Length L (Metric)	191
Width W (Imperial)	1.3
Width W (Metric)	33
Cable Ties	T120, T150, T250, T255, WS
Height H (Imperial)	5.3
Height H (Metric)	135
Tension Setting Tools	Adjustable
Cable Tie Width Max (Imperial)	0.5
Material	Plastic (PL) Metal (MET)
Material Shortcut	PL MET

ROHS Compliant Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 8205599000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[110-80004](#)