



POLES	PART No.	Dim. A	Dim. B	Dim. C	Dim. D
9	DB-9P	30.81	24.99	16.92	19.25
15	DB-15P	39.14	33.32	25.25	27.51
25	DB-25P	53.04	47.04	38.96	41.20
37	DB-37P	69.40	63.50	55.42	57.71

**MATERIAL & FINISHES**

INSULATOR - PBT GLASS FILLED UL94V-0  
 CONTACT- BRASS OR PHOSPHOR BRONZE  
 SHELL - STEEL  
 PLATING - CONTACT  
 SELECTIVE GOLD OVER NICKEL PLATED(CONTACT AREA)  
 TIN/LEAD OVER NICKEL PLATED(TAIL AREA)  
 - SHELL  
 TIN OR ZINC OVER COPPER PLATED

**ELECTRICAL CHARACTERISTICS**

CURRENT RATING : 3A  
 CONTACT RESISTANCE : 20mΩ MAX  
 INSULATION RESISTANCE : 1000MΩ AC 500V  
 DIELECTRIC VOLTAGE : 500V /MIN  
 OPERATING TEMPERATURE : -55°C TO+105°C

**TOLERANCE TABLE**

Dimension	Tolerance
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

LYP

2009-11-28

**Ckmtw** 深圳市灿科盟实业有限公司  
 CHANKLEMENT INDUSTRYCO., LTD

TITLE:  
 DB-XP 公头 焊线 传统式

P/N	UNIT	SCALE	REV.
/	mm	Free	A
FILE NO.	SCALE	REV.	HX00
Ckmtw-DB-0002	Free	A	