

216C6W

## Industrial Connector

## 2CMA166538R1000



Connector, earthing sleeve position 6h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue

## GENERAL

<b>Product Name</b>	Industrial Connector
<b>Product ID</b>	2CMA166538R1000
<b>Function</b>	Connector
<b>EAN</b>	7392696665384
<b>Catalog Description</b>	Connector, 6h, 16A, IP67, 2P+E
<b>Country of Origin</b>	Czech Republic (CZ)
<b>E-Number Finland</b>	2421654
<b>E-Number Norway</b>	2416361
<b>E-Number Sweden</b>	E2416361
<b>Standards</b>	IEC 60309-1, -2
<b>RoHS Status</b>	Following EU Directive 2011/65/EU

## TECHNICAL

<b>Product Main Type</b>	TC
<b>Color</b>	Blue
<b>Number of Poles</b>	3
<b>Clock Position</b>	6Hour
<b>Rated Current</b>	16 ampere
<b>Rated Voltage</b>	200 ... 250 volt
<b>Frequency</b>	50 hertz 60 hertz
<b>Degree of Protection</b>	IP67 IP69
<b>Cable Cross-Section</b>	1...2.5 mm <sup>2</sup>
<b>Housing Material</b>	Thermoplastic (PBT)
<b>Plug Angle</b>	Straight
<b>Product Group</b>	Tough&Safe

## DIMENSIONS

<b>Product Net Width</b>	70 millimetre
<b>Product Net Height</b>	80 millimetre
<b>Product Net Length</b>	151 millimetre
<b>Product Net Depth</b>	151 millimetre
<b>Product Net Weight</b>	0.244 kilogram

## PACKAGING

<b>Package Width</b>	95 millimetre
<b>Package Height</b>	175 millimetre
<b>Package Gross Weight</b>	0.28 kilogram
<b>Package Length</b>	95 millimetre
<b>Package Units</b>	box 1 piece