

316EP9

Industrial Plug

2CMA101958R1000

Industrial Plugs, 3P+E, 16A, 200 ... 250 V Clock Position Of
 Grounding Contact 9 hour Color code Blue



GENERAL

Product Name	Industrial Plug
Product ID	2CMA101958R1000
Function	Plug
EAN	73926919583
Catalog Description	Industrial Plugs, 3P+E, 16A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420065
E-Number Norway	1540709
E-Number Sweden	E2416167
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EP
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1...2.5 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	69 millimetre
Product Net Height	75 millimetre
Product Net Length	144 millimetre
Product Net Depth	144 millimetre
Product Net Weight	0.16 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.6 kilogram
Package Length	158 millimetre
Package Units	box 10 piece