

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300100864](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change A-Size Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 16 AWG, TPE Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family	Industrial Cordsets
Series	130010
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Double Ended
UPC	78678883800

Physical

Cable Diameter	10.67mm (.420")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold over Nickel
Net Weight	104.470/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	16
Wire/Cable Type	TC-ER

Electrical


Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

Material Info

Engineering Number 114030K12M010

Reference - Drawing Numbers

Sales Drawing 1300100863-000, SD-130010-016



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[130010 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300100621](#) [1300100615](#) [1300100678](#) [1300100280](#) [1300100205](#) [1300100245](#) [1300100240](#) [1300100143](#)
[1300100162](#) [1300100155](#) [1300100179](#) [1300100536](#) [1300100535](#) [1300100599](#) [1300100549](#) [1300100520](#)
[1300100596](#) [1300100519](#) [1300100526](#) [1300100473](#) [1300100491](#) [1300100869](#) [1300100803](#) [1300100360](#)
[1300101261](#) [1300101160](#) [1300101295](#) [1300101230](#) [1300101197](#) [1300101188](#) [1300101191](#) [1300101587](#)
[1300101585](#) [1300101039](#) [1300101606](#) [1300101006](#) [1300101001](#) [1300101394](#) [1300101316](#) [1300101301](#) [130010-](#)
[0864](#)