




Material	Polyamide
Operating Temperature	-40°C- +120°C(-40°F- +248°F)
Colours	grey (RAL7031), black (RAL9005)


RoHS

// rawmaterial according to UL94



Size DN	d mm	D mm	R mm	Number grey	Number black
6	6,5	10	15	1.527.0600.00	1.527.0601.00
10	10	13	25	1.527.0900.00	1.527.0901.00
12	12	15,8	35	1.527.1100.00	1.527.1101.00
14	14,2	18,4	35	1.527.1300.00	1.527.1301.00
17	16,5	21,2	40	1.527.1600.00	1.527.1601.00
23	23	28,4	45	1.527.2100.00	1.527.2101.00
29	29	34,5	55	1.527.2900.00	1.527.2901.00
37	36	42,5	65	1.527.3600.00	1.527.3601.00
50	48	54,5	80	1.527.4800.00	1.527.4801.00

Polyamide-Cut



Material	Housing made of plastic/ metal,artiskid rubber handle	
Colour	red	
// Tool for easy, exact and safe cutting of Polyamide-Conduits		
Cutting range	fitsto DN	Number
0-26mm	0-17	1.503.2600.00
0-63mm	0-50	1.503.6300.00