

332BS9

Wall mounted inlet

2CMA193324R1000



Wall mounted inlet, earthing sleeve position 9h, rated current 32A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA193324R1000
Function	Wall mounted inlet
EAN	7392696933247
Catalog Description	Surface inlet, 9h, 32A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417188
E-Number Norway	2417188
E-Number Sweden	E2417188
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EBS
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	85 millimetre
Product Net Height	116 millimetre
Product Net Length	163 millimetre
Product Net Depth	163 millimetre
Product Net Weight	0.27 kilogram

PACKAGING

Package Width	188 millimetre
Package Height	428 millimetre
Package Gross Weight	2.7 kilogram
Package Length	175 millimetre
Package Units	box 10 piece