

**APPLICATION NOTES**

1. Assembly identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Metric dimensions (mm) are in parentheses.


**TABLE I: Reference for Connector Shell Size**

Shell Size & Class	Thread UNJC-3B	A ±.003 (0.1)		B ±.015 (0.4)		C ±.015 (0.4)		D Max	E ±.030 (0.8)
3A	4-40	.625	(15.9)	.925	(23.5)	.641	(16.3)	.166 (4.2)	.325 (8.3)
7A	4-40	.719	(18.3)	1.019	(25.9)	.688	(17.5)	.166 (4.2)	.433 (11.0)
8A	4-40	.594	(15.1)	.880	(22.4)	.570	(14.5)	.166 (4.2)	.308 (7.8)
10A	4-40	.719	(18.3)	1.019	(25.9)	.720	(18.3)	.166 (4.2)	.433 (11.0)
10B	6-32	.812	(20.6)	1.312	(33.3)	.749	(19.0)	.183 (4.6)	.433 (11.0)
12A	4-40	.812	(20.6)	1.104	(28.0)	.855	(21.7)	.166 (4.2)	.530 (13.5)
12B	6-32	.938	(23.8)	1.312	(33.3)	.938	(23.8)	.183 (4.6)	.530 (13.5)
14A	4-40	.906	(23.0)	1.198	(30.4)	.984	(25.0)	.166 (4.2)	.624 (15.8)
14B	6-32	1.031	(26.2)	1.406	(35.7)	1.031	(26.2)	.183 (4.6)	.624 (15.8)
16A	4-40	.969	(24.6)	1.280	(32.5)	1.094	(27.8)	.166 (4.2)	.687 (17.4)
16B	6-32	1.125	(28.6)	1.500	(38.1)	1.125	(28.6)	.183 (4.6)	.687 (17.4)
18A	4-40	1.062	(27.0)	1.406	(35.7)	1.220	(31.0)	.166 (4.2)	.780 (19.8)
18B	6-32	1.203	(30.6)	1.578	(40.1)	1.234	(31.3)	.183 (4.6)	.780 (19.8)
19A	4-40	.906	(23.0)	1.192	(30.3)	.953	(24.2)	.166 (4.2)	.620 (15.7)
20A	4-40	1.156	(29.4)	1.535	(39.0)	1.345	(34.2)	.166 (4.2)	.874 (22.2)
20B	6-32	1.297	(32.9)	1.688	(42.9)	1.359	(34.5)	.183 (4.6)	.865 (22.0)
22A	4-40	1.250	(31.8)	1.665	(42.3)	1.478	(37.5)	.166 (4.2)	.968 (24.6)
22B	6-32	1.375	(34.9)	1.738	(44.1)	1.483	(37.7)	.183 (4.6)	.907 (23.0)
24A	6-32	1.500	(38.1)	1.891	(48.0)	1.560	(39.6)	.183 (4.6)	1.000 (25.4)
24B	6-32	1.375	(34.9)	1.785	(45.3)	1.595	(40.5)	.183 (4.6)	1.031 (26.2)
25A	6-32	1.500	(38.1)	1.891	(48.0)	1.658	(42.1)	.183 (4.6)	1.125 (28.6)
27A	4-40	.969	(24.6)	1.255	(31.9)	1.094	(27.8)	.166 (4.2)	.683 (17.3)
28A	6-32	1.562	(39.7)	2.000	(50.8)	1.820	(46.2)	.183 (4.6)	1.125 (28.6)
32A	6-32	1.750	(44.5)	2.312	(58.7)	2.062	(52.4)	.183 (4.6)	1.188 (30.2)
36A	6-32	1.938	(49.2)	2.500	(63.5)	2.312	(58.7)	.183 (4.6)	1.375 (34.9)
37A	4-40	1.187	(30.1)	1.500	(38.1)	1.281	(32.5)	.166 (4.2)	.874 (22.2)
61A	4-40	1.437	(36.5)	1.812	(46.0)	1.594	(40.5)	.166 (4.2)	1.602 (40.7)

Dimensions in inches (millimeters) and are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[M85049/127-01](#) [M85049/127-02](#) [M85049/95-25A](#) [M85049/80-8](#)