










FIBOX MNX ABS

FIBOX MNX ABS ABS: IP 66/67 and IP 66, IK 07	Z mm	C mm	Including: Enclosure cover with cover screws and wing heads for cover screws, base with mounting plate screws and gasket.				B x A
			ORDER SYMBOL		ORDER SYMBOL		L x S
			Grey cover		Smoked transparent cover		mm
ABS 95 L / ABS 95 H Y x X 100 mm 100 mm 	35	28.8	ABS 95/35 LG		ABS 95/35 LT	B x A	
	50	45.6	ABS 95/50 LG		ABS 95/50 LT	70 x 45	
	60	53.8	ABS 95/60 HG		ABS 95/60 HT	L x S	
	75	70.6	ABS 95/75 HG		ABS 95/75 HT	83.5 x 83.5	
ABS 100 L Y x X 130 mm 80 mm 	35	24.1	ABS 100/35 LG		ABS 100/35 LT	B x A	
	50	41.0	ABS 100/50 LG		ABS 100/50 LT	90 x 40	
	75	61.0	ABS 100/75 LG		ABS 100/75 LT	L x S	
	100	90.9	ABS 100/100 LG		ABS 100/100 LT	113.5 x 63.5	
ABS 100 H Y x X 130 mm 80 mm 	60	44.5	PC 100/60 HG		ABS 100/60 HT	B x A	
	75	61.0	PC 100/75 HG		ABS 100/75 HT	90 x 40	
	100	86.3	PC 100/100 HG		ABS 100/100 HT	L x S	
	125	111.3	PC 100/125 HG		ABS 100/125 HT	113.5 x 63.5	
ABS 125 L Y x X 130 mm 130 mm 	35	24.0	ABS 125/35 LG		ABS 125/35 LT	B x A	
	50	40.9	ABS 125/50 LG		ABS 125/50 LT	90 x 90	
	75	65.9	ABS 125/75 LG		ABS 125/75 LT	L x S	
	100	90.9	ABS 125/100 LG		ABS 125/100 LT	113.5 x 113.5	
ABS 125 H Y x X 130 mm 130 mm 	60	44.4	ABS 125/60 HG		ABS 125/60 HT	B x A	
	75	61.0	ABS 125/75 HG		ABS 125/75 HT	90 x 90	
	100	86.2	ABS 125/100 HG		ABS 125/100 HT	L x S	
	125	111.3	ABS 125/125 HG		ABS 125/125 HT	113.5 x 113.5	
ABS 150 L Y x X 180 mm 130 mm 	35	23.6	ABS 150/35 LG		ABS 150/35 LT	B x A	
	50	41.0	ABS 150/50 LG		ABS 150/50 LT	140 x 90	
	75	65.9	ABS 150/75 LG		ABS 150/75 LT	L x S	
	100	90.9	ABS 150/100 LG		ABS 150/100 LT	163.5 x 113.5	
125	115.5	ABS 150/125 LG		ABS 150/125 LT			
ABS 150 H Y x X 180 mm 130 mm 	60	44.0	ABS 150/60 HG		ABS 150/60 HT	B x A	
	75	61.3	ABS 150/75 HG		ABS 150/75 HT	140 x 90	
	100	86.3	ABS 150/100 HG		ABS 150/100 HT	L x S	
	125	111.3	ABS 150/125 HG		ABS 150/125 HT	163.5 x 113.5	
150	135.9	ABS 150/150 HG		ABS 150/150 HT			
ABS 175 H Y x X 180 mm 180 mm 	60	44.0	ABS 175/60 HG		ABS 175/60 HT	B x A	
	75	61.0	ABS 175/75 HG		ABS 175/75 HT	140 x 140	
	100	86.3	ABS 175/100 HG		ABS 175/100 HT	L x S	
	125	111.0	ABS 175/125 HG		ABS 175/125 HT	163.5 x 163.5	
150	135.9	ABS 175/150 HG		ABS 175/150 HT			
ABS 200 H Y x X 255 mm 180 mm  ABS 200 XH	63	47.5	ABS 200/63 HG		ABS 200/63 HT	B x A	
	75	61.2	ABS 200/75 HG		ABS 200/75 HT	215 x 140	
	100	86.3	ABS 200/100 HG		ABS 200/100 HT	L x S	
	150	135.9	ABS 200/150 HG		ABS 200/150 HT	238.5 x 163.5	
	88	71.5	ABS 200/88 XHG		ABS 200/88 XHT		
	100	86.8	ABS 200/100 XHG		ABS 200/100 XHT		
125	111.9	ABS 200/125 XHG		ABS 200/125 XHT			
175	161.5	ABS 200/175 XHG		ABS 200/175 XHT			

External height **Y** External width **X** External depth **Z** Free internal mounting height **C** Mounting plate assembly **B x A** Wall mounting **L x S**

L (low base) enclosure with the low 25 mm base, H (high base) = enclosure with the high 50 mm base, XH (extra high base) = enclosure with the extra high 75 mm base.
 LT smoked transparent cover with black cover screws and black wing heads, LG grey cover with grey cover screws and grey wing heads.