


GF Piping Systems Datasheet

valid from
9/9/09

Malleable cast iron fittings

2a Short bend 90°, ISO/EN D1



	Dim. [inch]	EN	Code	SP	kg	a [mm]	z [mm]
B	1/4	•	770 012 102	80	0.061	30	20
G	1/4	•	770 012 202	80	0.064	30	20
B	3/8	•	770 012 103	10	0.086	36	26
G	3/8	•	770 012 203	10	0.122	36	26
B	1/2	•	770 012 104	10	0.164	45	32
G	1/2	•	770 012 204	10	0.170	45	32
B	3/4	•	770 012 105	10	0.245	50	35
G	3/4	•	770 012 205	10	0.253	50	35
B	1	•	770 012 106	30	0.331	63	46
G	1	•	770 012 206	30	0.333	63	46
B	1 1/4	•	770 012 107	30	0.612	76	57
G	1 1/4	•	770 012 207	30	0.653	76	57
B	1 1/2	•	770 012 108	25	0.708	85	66
G	1 1/2	•	770 012 208	25	0.822	85	66
B	2	•	770 012 109	12	1.306	102	78
G	2	•	770 012 209	12	1.369	102	78
B	2 1/2	-	770 012 110	8	2.020	115	88
G	2 1/2	-	770 012 210	8	2.100	115	88
B	3	-	770 012 111	6	2.565	127	97
G	3	-	770 012 211	6	2.630	127	97
B	4	-	770 012 112	2	6.115	165	129
G	4	-	770 012 212	2	6.290	165	129

The technical data are not binding and not expressly warranted characteristics of the goods. They are subject to change. Our General Conditions of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland
 Phone +41 -(0)52-631 1111
 e-mail: info.ps@georgfischer.com
 Internet: <http://www.piping.georgfischer.com>