

## 467BR - Metric fast open end combined ratchets





### Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691

### Description:

- Standard open end combined ratchets: for all current applications.
- Compact lever reversible ratchet mechanism.
- 5° increments.
- Ring head angled by 15°.
- Open end head angled by 15°.
- Metric dimensions: 8 to 19 mm.
- Satin chrome finish.



	A [mm]	Length L [mm]	Thickness E [mm]	Thickness E1 [mm]	Thickness E2 [mm]	Head Height C [mm]	Head Width B [mm]	Head Width B1 [mm]	Weight [Kg]
<b>467BR.10</b>	10.0	158.0	5.1	7.3	3.4	10.4	22.7	20.2	0.049
<b>467BR.11</b>	11.0	165.0	5.2	7.7	3.5	10.6	23.7	22.0	0.058
<b>467BR.12</b>	12.0	171.0	5.4	8.2	3.8	11.3	26.8	23.2	0.069
<b>467BR.13</b>	13.0	178.0	5.7	8.6	4.3	12.2	28.4	25.3	0.086
<b>467BR.14</b>	14.0	190.0	5.9	9.0	4.3	13.0	30.8	27.0	0.1
<b>467BR.16</b>	16.0	208.0	6.6	9.9	5.3	14.1	34.9	30.0	0.138
<b>467BR.17</b>	17.0	225.0	6.6	10.3	5.4	15.4	36.8	31.7	0.162
<b>467BR.18</b>	18.0	236.0	7.4	10.7	5.8	15.6	38.4	32.8	0.183
<b>467BR.19</b>	19.0	247.0	7.4	11.2	6.0	16.0	41.2	33.9	0.212
<b>467BR.8</b>	10.0	140.0	4.6	6.5	3.1	8.2	18.6	16.8	0.034