

D-Sub M AWG 22-26 HMC contact Cat.7 mod.



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 200 5576
Specification	D-Sub M AWG 22-26 HMC contact Cat.7 mod.
HARTING eCatalogue	https://b2b.harting.com/09932005576

Identification

Category	Contacts
Series	D-Sub
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.52 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Contact resistance	≤10 mΩ
Stripping length	4 mm
Performance level	1 acc. to CECC 75301-802
Mating cycles with other HMC components	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	100
Net weight	0.22 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09932005576](#)