

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sealing frame, with screw locking, design: B24, Number of cable seals (small): 10, material: PA (halogen-free), color: black, length: 147 mm, width: 58 mm, height: 20 mm

Your advantages

- Can also be used for standard panel cutouts for heavy-duty industrial connectors

Commercial data

Item number	0801658
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	BF7CAX
Catalog page	Page 677 (C-2-2019)
GTIN	4046356674140
Weight per piece (including packing)	193.6 g
Weight per piece (excluding packing)	173.3 g
Customs tariff number	39269097
Country of origin	PL

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Technical data

Notes

General	Mounting screws not supplied as standard. The maximum width of the panel cutout must not exceed 51 mm (instead of 35 mm for heavy-duty industrial connectors).
---------	--

Product properties

Type	B24
Product type	Frame for cable sleeves
Frame type	Sealing frame

Dimensions

Dimensional drawing	
Width	58 mm
Height	20 mm
Length	147 mm
Drill hole distance, horizontal	32 mm
Drill hole distance, vertical	130 mm
Hole diameter	5.5 mm

Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	113 mm

Material specifications

Material	PA
Flammability rating according to UL 94	V0

Characteristics

Number of cable seals	2 ... 10 (small seals, depending on the number of large seals installed)
	0 ... 2 (large seals, depending on the number of small seals installed)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
	IP65
Ambient temperature (operation)	-40 °C ... 120 °C (static)

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Mounting

Assembly instructions	<p>M4 locking screw with 3 mm Allen screw head, 3 ... 4 Nm torque, 1 large sleeve requires the space of 4 small sleeves, mounting screw: M4 (ISO 4762/DIN 912), 1.8 Nm torque</p> <p>The flat gasket supplied should be inserted between the wall and the sealing frame in the case of wall mounting. IP54: for vertical sealing frame mounting/for horizontal sealing frame mounting (downward cable outlet direction). IP65: when using the CES-SRC-BK / CES-LRC-BK cone sleeve, for vertical mounting/horizontal mounting (downward cable outlet direction) of the sealing frame directly on the housing panel, and use of a 3.6 mm wide cable binder (e.g., item 3240744).</p>
-----------------------	--


CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>


Drawings

Dimensional drawing



Mounting cutout

Dimensional drawing



Dimensional drawing

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801658>



cUL Recognized

Approval ID: NITW8.E255026



UL Recognized

Approval ID: NITW2.E255026

DNV

Approval ID: TAE00003VJ

cULus Recognized

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Classifications

ECLASS

ECLASS-11.0	27142421
ECLASS-12.0	27142421
ECLASS-13.0	27142421

ETIM

ETIM 8.0	EC000211
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

CES-B24-SFFS-PLBK - Sealing frame



0801658

<https://www.phoenixcontact.com/us/products/0801658>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



Accessories

CES-B24-WRG-BK - Flat gasket

0801727

<https://www.phoenixcontact.com/us/products/0801727>

Flat gasket made of NBR, size B24



CES-SFFS-H - Screw

0801728

<https://www.phoenixcontact.com/us/products/0801728>

M4 replacement screw with 4 mm Allen screw head for sealing frame with screw locking



CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-B24-SF-PLBK - Snap-on frame

0801647

<https://www.phoenixcontact.com/us/products/0801647>




Snap-on frame, design: B24, material: PA (halogen-free), color: black, length: 155 mm, width: 64 mm, height: 39 mm

CES-STPG-GY-2 - Cable sleeve

0801672

<https://www.phoenixcontact.com/us/products/0801672>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 1 mm ... 2 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-3 - Cable sleeve

0801673

<https://www.phoenixcontact.com/us/products/0801673>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 2 mm ... 3 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-4 - Cable sleeve

0801674

<https://www.phoenixcontact.com/us/products/0801674>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 3 mm ... 4 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-5 - Cable sleeve

0801675

<https://www.phoenixcontact.com/us/products/0801675>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 4 mm ... 5 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-6 - Cable sleeve

0801676

<https://www.phoenixcontact.com/us/products/0801676>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 5 mm ... 6 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-7 - Cable sleeve

0801677

<https://www.phoenixcontact.com/us/products/0801677>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 6 mm ... 7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-8 - Cable sleeve

0801679

<https://www.phoenixcontact.com/us/products/0801679>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 7 mm ... 8 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-9 - Cable sleeve

0801680

<https://www.phoenixcontact.com/us/products/0801680>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 8 mm ... 9 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-10 - Cable sleeve

0801682

<https://www.phoenixcontact.com/us/products/0801682>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 9 mm ... 10 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-11 - Cable sleeve

0801683

<https://www.phoenixcontact.com/us/products/0801683>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 10 mm ... 11 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-12 - Cable sleeve

0801684

<https://www.phoenixcontact.com/us/products/0801684>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 11 mm ... 12 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-13 - Cable sleeve

0801685

<https://www.phoenixcontact.com/us/products/0801685>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 12 mm ... 13 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-14 - Cable sleeve

0801686

<https://www.phoenixcontact.com/us/products/0801686>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 13 mm ... 14 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-15 - Cable sleeve

1410521

<https://www.phoenixcontact.com/us/products/1410521>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 13.9 mm ... 14.2 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-16 - Cable sleeve

1410534

<https://www.phoenixcontact.com/us/products/1410534>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 14.9 mm ... 15.2 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-17 - Cable sleeve

1410547

<https://www.phoenixcontact.com/us/products/1410547>




Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 15.9 mm ... 16.2 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-LTPG-GY-15 - Cable sleeve

0801687

<https://www.phoenixcontact.com/us/products/0801687>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 14 mm ... 15 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-16 - Cable sleeve

0801688

<https://www.phoenixcontact.com/us/products/0801688>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 15 mm ... 16 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-17 - Cable sleeve

0801689

<https://www.phoenixcontact.com/us/products/0801689>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 16 mm ... 17 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-18 - Cable sleeve

0801690

<https://www.phoenixcontact.com/us/products/0801690>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 17 mm ... 18 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-19 - Cable sleeve

0801691

<https://www.phoenixcontact.com/us/products/0801691>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 18 mm ... 19 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-20 - Cable sleeve

0801692

<https://www.phoenixcontact.com/us/products/0801692>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 19 mm ... 20 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-21 - Cable sleeve

0801693

<https://www.phoenixcontact.com/us/products/0801693>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 20 mm ... 21 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-22 - Cable sleeve

0801695

<https://www.phoenixcontact.com/us/products/0801695>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 21 mm ... 22 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-23 - Cable sleeve

0801696

<https://www.phoenixcontact.com/us/products/0801696>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 22 mm ... 23 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-24 - Cable sleeve

0801697

<https://www.phoenixcontact.com/us/products/0801697>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 23 mm ... 24 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-25 - Cable sleeve

0801698

<https://www.phoenixcontact.com/us/products/0801698>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 24 mm ... 25 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-26 - Cable sleeve

0801699

<https://www.phoenixcontact.com/us/products/0801699>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 25 mm ... 26 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-27 - Cable sleeve

0801700

<https://www.phoenixcontact.com/us/products/0801700>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 26 mm ... 27 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-28 - Cable sleeve

0801701

<https://www.phoenixcontact.com/us/products/0801701>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 27 mm ... 28 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-29 - Cable sleeve

0801702

<https://www.phoenixcontact.com/us/products/0801702>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 28 mm ... 29 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-30 - Cable sleeve

0801703

<https://www.phoenixcontact.com/us/products/0801703>




Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 29 mm ... 30 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-31 - Cable sleeve

0801705

<https://www.phoenixcontact.com/us/products/0801705>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 30 mm ... 31 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY-32 - Cable sleeve

0801706

<https://www.phoenixcontact.com/us/products/0801706>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 31 mm ... 32 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-LTPG-GY-33 - Cable sleeve

0801707

<https://www.phoenixcontact.com/us/products/0801707>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 32 mm ... 33 mm, material: SEBS (halogen-free), color: gray, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-2X3 - Cable sleeve

1410424

<https://www.phoenixcontact.com/us/products/1410424>




Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 2.4 mm ... 2.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-2X4 - Cable sleeve

1410438

<https://www.phoenixcontact.com/us/products/1410438>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 3.4 mm ... 3.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-2X5 - Cable sleeve

0801708

<https://www.phoenixcontact.com/us/products/0801708>




Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 4 mm ... 5 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-2X6 - Cable sleeve

0801709

<https://www.phoenixcontact.com/us/products/0801709>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 5 mm ... 6 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-2X7 - Cable sleeve

1410110

<https://www.phoenixcontact.com/us/products/1410110>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 6.4 mm ... 6.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-2X8 - Cable sleeve

1410123

<https://www.phoenixcontact.com/us/products/1410123>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 7.4 mm ... 7.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-2X9 - Cable sleeve

1410440

<https://www.phoenixcontact.com/us/products/1410440>




Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 8.4 mm ... 8.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-4X3 - Cable sleeve

0801710

<https://www.phoenixcontact.com/us/products/0801710>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 2 mm ... 3 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-4X4 - Cable sleeve

0801711

<https://www.phoenixcontact.com/us/products/0801711>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 3 mm ... 4 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY-4X5 - Cable sleeve

1410136

<https://www.phoenixcontact.com/us/products/1410136>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 4.4 mm ... 4.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-STPG-GY-4X6 - Cable sleeve

1410149

<https://www.phoenixcontact.com/us/products/1410149>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 5.4 mm ... 5.7 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-2 - Cable sleeve

0801635

<https://www.phoenixcontact.com/us/products/0801635>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 1 mm ... 2 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-3 - Cable sleeve

0801633

<https://www.phoenixcontact.com/us/products/0801633>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 2 mm ... 3 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-4 - Cable sleeve

0801632

<https://www.phoenixcontact.com/us/products/0801632>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 3 mm ... 4 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-5 - Cable sleeve

0801630

<https://www.phoenixcontact.com/us/products/0801630>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 4 mm ... 5 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-6 - Cable sleeve

0801628

<https://www.phoenixcontact.com/us/products/0801628>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 5 mm ... 6 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-7 - Cable sleeve

0801627

<https://www.phoenixcontact.com/us/products/0801627>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 6 mm ... 7 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-8 - Cable sleeve

0801625

<https://www.phoenixcontact.com/us/products/0801625>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 7 mm ... 8 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-9 - Cable sleeve

0801622

<https://www.phoenixcontact.com/us/products/0801622>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 8 mm ... 9 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-10 - Cable sleeve

0801620

<https://www.phoenixcontact.com/us/products/0801620>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 9 mm ... 10 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-11 - Cable sleeve

0801618

<https://www.phoenixcontact.com/us/products/0801618>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 10 mm ... 11 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-12 - Cable sleeve

0801617

<https://www.phoenixcontact.com/us/products/0801617>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 11 mm ... 12 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-13 - Cable sleeve

0801616

<https://www.phoenixcontact.com/us/products/0801616>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 12 mm ... 13 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-14 - Cable sleeve

0801615

<https://www.phoenixcontact.com/us/products/0801615>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 13 mm ... 14 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-15 - Cable sleeve

1410563

<https://www.phoenixcontact.com/us/products/1410563>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 14 mm ... 15 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-16 - Cable sleeve

1410576

<https://www.phoenixcontact.com/us/products/1410576>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 15 mm ... 16 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-17 - Cable sleeve

1410589

<https://www.phoenixcontact.com/us/products/1410589>



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 16 mm ... 17 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-LRG-BK-15 - Cable sleeve

0801619

<https://www.phoenixcontact.com/us/products/0801619>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 14 mm ... 15 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-16 - Cable sleeve

0801621

<https://www.phoenixcontact.com/us/products/0801621>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 15 mm ... 16 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-17 - Cable sleeve

0801624

<https://www.phoenixcontact.com/us/products/0801624>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 16 mm ... 17 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-18 - Cable sleeve

0801626

<https://www.phoenixcontact.com/us/products/0801626>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 17 mm ... 18 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-19 - Cable sleeve

0801629

<https://www.phoenixcontact.com/us/products/0801629>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 18 mm ... 19 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-20 - Cable sleeve

0801631

<https://www.phoenixcontact.com/us/products/0801631>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 19 mm ... 20 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-21 - Cable sleeve

0801634

<https://www.phoenixcontact.com/us/products/0801634>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 20 mm ... 21 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-22 - Cable sleeve

0801637

<https://www.phoenixcontact.com/us/products/0801637>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 21 mm ... 22 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-23 - Cable sleeve

0801638

<https://www.phoenixcontact.com/us/products/0801638>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 22 mm ... 23 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-24 - Cable sleeve

0801639

<https://www.phoenixcontact.com/us/products/0801639>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 23 mm ... 24 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-25 - Cable sleeve

0801640

<https://www.phoenixcontact.com/us/products/0801640>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 24 mm ... 25 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-26 - Cable sleeve

0801643

<https://www.phoenixcontact.com/us/products/0801643>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 25 mm ... 26 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-27 - Cable sleeve

0801644

<https://www.phoenixcontact.com/us/products/0801644>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 26 mm ... 27 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-28 - Cable sleeve

0801646

<https://www.phoenixcontact.com/us/products/0801646>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 27 mm ... 28 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-29 - Cable sleeve

0801648

<https://www.phoenixcontact.com/us/products/0801648>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 28 mm ... 29 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-30 - Cable sleeve

0801650

<https://www.phoenixcontact.com/us/products/0801650>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 29 mm ... 30 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-31 - Cable sleeve

0801653

<https://www.phoenixcontact.com/us/products/0801653>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 30 mm ... 31 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK-32 - Cable sleeve

0801654

<https://www.phoenixcontact.com/us/products/0801654>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 31 mm ... 32 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-LRG-BK-33 - Cable sleeve

0801656

<https://www.phoenixcontact.com/us/products/0801656>



Cable sleeve, large, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 32 mm ... 33 mm, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-2X3 - Cable sleeve

1410398

<https://www.phoenixcontact.com/us/products/1410398>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 2 mm ... 3 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-2X4 - Cable sleeve

1410408

<https://www.phoenixcontact.com/us/products/1410408>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 3 mm ... 4 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-2X5 - Cable sleeve

0801657

<https://www.phoenixcontact.com/us/products/0801657>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 4 mm ... 5 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-2X6 - Cable sleeve

0801664

<https://www.phoenixcontact.com/us/products/0801664>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 5 mm ... 6 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-2X7 - Cable sleeve

1410084

<https://www.phoenixcontact.com/us/products/1410084>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 6 mm ... 7 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-2X8 - Cable sleeve

1410097

<https://www.phoenixcontact.com/us/products/1410097>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 7 mm ... 8 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-2X9 - Cable sleeve

1410411

<https://www.phoenixcontact.com/us/products/1410411>



Cable sleeve, small, no. of conductors: 2, type: Round cable, slotted, external cable diameter: 2x 8 mm ... 9 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-4X3 - Cable sleeve

0801665

<https://www.phoenixcontact.com/us/products/0801665>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 2 mm ... 3 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-4X4 - Cable sleeve

0801666

<https://www.phoenixcontact.com/us/products/0801666>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 3 mm ... 4 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-SRG-BK-4X5 - Cable sleeve

1410107

<https://www.phoenixcontact.com/us/products/1410107>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 4 mm ... 5 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK-4X6 - Cable sleeve

1410152

<https://www.phoenixcontact.com/us/products/1410152>



Cable sleeve, small, no. of conductors: 4, type: Round cable, slotted, external cable diameter: 4x 5 mm ... 6 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-LRC-BK - Cable sleeve

0801719

<https://www.phoenixcontact.com/us/products/0801719>



Cable sleeve, large, no. of conductors: 1, type: Round cable, closed, external cable diameter: 1x 7 mm ... 24 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-LRG-BK - Blind sleeve

0801671

<https://www.phoenixcontact.com/us/products/0801671>

Blind sleeve, large, no. of conductors: 0, type: Blind sleeve, closed, material: NBR, color: black, length: 53 mm, width: 39 mm, height: 17 mm



CES-SRC-BK - Cable sleeve

0801718

<https://www.phoenixcontact.com/us/products/0801718>

Cable sleeve, small, no. of conductors: 1, type: Round cable, closed, external cable diameter: 1x 2 mm ... 11 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm



CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



CES-SRG-BK - Blind sleeve

0801670

<https://www.phoenixcontact.com/us/products/0801670>




Blind sleeve, small, no. of conductors: 0, type: Blind sleeve, closed, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-STPG-GY - Blind sleeve

0801715

<https://www.phoenixcontact.com/us/products/0801715>



Blind sleeve, small, no. of conductors: 0, type: Blind sleeve, closed, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

CES-B24-SFFS-PLBK - Sealing frame

0801658


<https://www.phoenixcontact.com/us/products/0801658>



CES-LTPG-GY - Blind sleeve

0801716

<https://www.phoenixcontact.com/us/products/0801716>



Blind sleeve, large, no. of conductors: 0, type: Blind sleeve, closed, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

SF-M BH - Screwdriver

1212070

<https://www.phoenixcontact.com/us/products/1212070>



Bit screwdriver, with 1/4" quick-action chuck, handle length 119 mm, 2-component handle, with non-slip grip, suitable for bits according to DIN 3126-C 6.3 and E 6.3/ISO 1173, magnetic

CES-B24-SFFS-PLBK - Sealing frame

0801658

<https://www.phoenixcontact.com/us/products/0801658>



SF-BIT-HEX 3-50 - Screw insert

1212647

<https://www.phoenixcontact.com/us/products/1212647>



Screw bit, hexagon, E6.3-1/4" drive, size: Hex 3 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com