




**C7J18 (JAP)**

Country of Origin: China  
 Manufacturer: SUNNY  
 Operating Temperature: 0 ÷ 40[°C]  
 Length/cord : 1.8m / 2x0,75 mm2  
 Approvals : PSE /JPN JET **RoHS**



Application	For Class II. Appliances	
JAPAN Plug typ A	NEMA 1-15 7A/125V	
C7 Plug	7A/125V	
Cable construction	VCTFK	
Max current	7A	
Insulation material	PVC	
Rated voltage	300V 60°C	
WEIGHT / PACKING	1pc	N.W.: 104g / pc
	Box	0.56 x 0.36 x 0.20 [m]
		150 pcs / 1box
		G.W.: 16.3kg / box