

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936040103](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 100 x 100 x 80mm Outside Dimensions, Grey RAL 7001](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------|---|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93604 |
| IP Rating | IP66, IP69 |
| Overview | GWconnect Heavy Duty Connectors (HDC) |
| Product Category | Die-cast Enclosures |
| Product Name | GWconnect |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2 |
| Type | STD |
| UPC | 887191873282 |

Physical

| | |
|-------------------------------|------------------------|
| Enclosure Coating | Polyester Powder |
| Enclosure Color | Grey RAL 7001 |
| Internal Dimensions | 92 x 92 x 73mm |
| Material - Enclosure | Die-cast Aluminum |
| Mounting Style | Internal Through Holes |
| Net Weight | 615.000/g |
| Outside Dimensions | 100 x 100 x 80mm |
| Packaging Type | Carton |
| Temperature Range - Operating | -40° to +125°C |

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 8100.8015.0 |
|--------------------|-------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93604 Series](#)

Use With

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION