

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200868645](#)

Status: **Active**

Overview: [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)

Description: Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Male (90°) to Pigtail, 24 AWG, WSOR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	889056003506

Physical

Cable Diameter	4.50mm (.177")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	WSOR

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

Material Info

Engineering Number 403007B41M050

Reference - Drawing Numbers

Sales Drawing SD-120086-008



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120086 Series](#)