



5

4



3

2

1



PCB Layout, Component side,
thickness 1.6 mm



SPECIFICATION

Performance level	PL2
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

D


C

B

A

09641247233	M3		36283	12/01/12	SD					
09641247232	UNC 4-40		33240	13/10/05	JMDR					
Part number	Nut thread		31058	8-JUL-02	CV					
			Mod.	Dot.	Name					

	Dot.	Name
Detail.	13/10/05	JMDR
Insp.	12/01/12	JB
Stand.		



All Dim. in mm
Orig. Size DIN A 4

D-Sub, male, angled, 9 Poles,
solder pins, brackets,
clinch nuts and board-locks

Mo?Mstab/
Scale

1.5:1

HARTING EURL
F-95972 Paris



TB 0964124723x

Blatt/ Page

1 / 4

Sub.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09641247233](#) [09641247232](#)