




DESCRIPTION: 988 SERIES BACK SHELL KIT




STRAIN RELIEF CLAMP




STRAIN RELIEF SCREW



BACK SHELL SCREW



SPRING CLIP



| No. OF PINS                   | DIMENSIONS    |               |               |               |                               |               |
|-------------------------------|---------------|---------------|---------------|---------------|-------------------------------|---------------|
|                               | A             | B             | C             | D             | E                             | F             |
| 50                            | 1.988 [50.50] | 1.594 [40.50] | 0.422 [10.71] | 0.498 [12.65] | 0.354 [9.00] - 0.433 [11.00]  | 1.445 [36.70] |
| 68                            | 2.409 [61.20] | 2.020 [51.30] | 0.421 [10.70] | 0.480 [12.20] | 0.433 [11.00] - 0.551 [14.00] | 2.453 [36.90] |
| ALL TOLERANCES = 0.012 [0.30] |               |               |               |               |                               |               |

**MATERIAL:**

- BACK SHELL: ZINC PLATED NICKEL OVER COPPER
- JACKSCREWS: STEEL, NICKEL PLATED OVER COPPER
- SCREWS: STEEL, NICKEL PLATED OVER COPPER
- CLAMP: STEEL, NICKEL PLATED

**KIT INCLUDES:**

- 2-BACK SHELL HALVES
- 1-STRAIN RELIEF CLAMP
- 1-CONNECTOR (SOLDER LATCH)
- 2-STRAIN RELIEF SCREWS (FLAT HEAD M2.6)
- 2-BACK SHELL SCREWS (FLAT HEAD M2.6)
- 2-SPRING CLIPS

**BACK SHELL KIT  
PART NUMBER  
988-YYY-130L121**

- SERIES \_\_\_\_\_
- POSITIONS \_\_\_\_\_
- 050 \_\_\_\_\_
- 068 \_\_\_\_\_
- CONTACTS \_\_\_\_\_
- SOLDER \_\_\_\_\_
- MATERIAL \_\_\_\_\_
- 30 = DIE CAST (NICKEL)
- RoHS COMPLIANT \_\_\_\_\_
- L = LOW TEMP. PROCESS \_\_\_\_\_
- COLOR \_\_\_\_\_
- 12 = METAL(IZED)
- PUT-UP \_\_\_\_\_
- 1 = KIT

RoHS COMPLIANT

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

C. SMITH

DATE:

04/18/2008

NorComp

SCALE:

NTS

SHEET

1

OF

3

REV

5

DWG NO.




988-YYY-130L121

DESCRIPTION: CONNECTOR FOR 988 SERIES BACK SHELL KIT

| No. OF PINS | DIMENSIONS    |               |              |
|-------------|---------------|---------------|--------------|
|             | A             | B             | C            |
| 50          | 1.545 [39.30] | 1.372 [34.85] | 0.366 [9.30] |
| 68          | 1.996 [50.70] | 1.825 [46.35] | 0.366 [9.30] |


**MATERIAL:**  
 HOUSING: THREMOPLASTIC, BLACK, P.B.T. UL94V-0  
 CONTACTS: PHOSPHOR BRONZE, 5u" GOLD MATING AREA  
 FRONT SHELL: STEEL, NICKEL PLATED OVER COPPER

**ELECTRICAL:**  
 CURRENT RATING: 1 AMPS  
 INSULATOR RESISTANCE: 500 MOHMS Min.  
 DIELECTRIC WITHSTANDING: 500VAC  
 CONTACT RESISTANCE: 35 mOhms Max.  
 OPERATING TEMPERATURE: -55° ~ +85° C



RoHS COMPLIANT



UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING

|                                                                                    |                                                                                                                                                                                             |                            |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|
|  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWN:<br><b>C. SMITH</b>  |
|                                                                                    |                                                                                                                                                                                             | DATE:<br><b>04/18/2008</b> |





**NorComp**

|               |            |                 |          |
|---------------|------------|-----------------|----------|
| SCALE:<br>NTS | SHEET<br>2 | OF<br>3         | REV<br>5 |
| DWG NO.       |            | 988-YYY-130L121 |          |

**50 POSITION**




**68 POSITION**



RoHS COMPLIANT

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING

|                                                                                    |                                                                                                                                                                                             |                            |
|------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|
|  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWN:<br><b>C. SMITH</b>  |
|                                                                                    |                                                                                                                                                                                             | DATE:<br><b>04/18/2008</b> |

NorComp

|                                |                                  |                 |
|--------------------------------|----------------------------------|-----------------|
| SCALE:<br><b>NTS</b>           | SHEET<br><b>3</b> OF<br><b>3</b> | REV<br><b>5</b> |
| DWG NO. <b>988-YYY-130L121</b> |                                  |                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[988-050-130L121](#)