

## Flanged Spade Terminals

## Flanged Spade Terminals 159-2230, 159-2236, 159-2238







Dimensions: In.

SPECIFICATIONS	
Туре:	flanged spade
Acceptable wire size:	22~16AWG
Voltage:	600V max. @ 75°C
Current:	19A max.
Insulation:	vinyl
Material:	copper
Material thickness:	.030"
Insulation color:	red
Stud size:	#6(159-2236), #8(159-2238), #10(159-2230)

Date Last Revised: 5-10-05

Available from Mouser Electronics 1-800-346-6873 www.mouser.com

KC-300735

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Kobiconn:

<u>159-1213</u> <u>159-2238</u> <u>159-2230</u> <u>159-1210</u>