

TORQUE WRENCH 1/2 INCH DR REV 210NM

Item ID: 1292AG-ER



- 1/2" drive bi-directional torque wrench covering 40-210Nm
- Equipped with an in-built angular gauge for easier after tightening of stretch bolts (TTY torque to yield fasteners)
- Click type mechanism with easily recognisable signal when the required torque is reached
- Simple to adjust and easy to read Nm scale
- Additional ft/lb reference scale (range 30-150 ft/lb)
- Clearly marked with three bands to show the correct place on the handle where pressure should be applied to give a more accurate torque reading
- Twist locking facility to ensure the set torque is maintained
- Push through square drive for use on clockwise and anti-clockwise fastenings
- Reversible 24 teeth ratchet mechanism (DIN3122) giving 15° increments for strength and for added reference when torqueing stretch bolts
- Accurate to +/- 4% and conforms to ISO6789 for assured reliability and accuracy
- Individually tested and certified at the time of manufacture
- Each torque wrench has it's own individual certification number for easier quality control management
- Supplied in a handy storage case

<u>Length (mm):</u>	<u>90</u>
<u>Width (mm):</u>	<u>560</u>
<u>Height (mm):</u>	<u>70</u>
<u>Weight (kg):</u>	<u>2.085</u>

Technical changes and errors may occur

WWW.TENGOOLS.COM



Get organised™