



DATASHEET

FLEXIBLE TOGGLE LATCH 40040 ZI



DESCRIPTION:

Latch with a flat profile that is especially suitable for use in areas of low clearance

The latch folds flat in the open position to minimize the risk of accidental damage

Can be used for gripping in a groove without use of the catch plate

Weld or M3 screw fixing

Approximate mounting dimension with catch plate = 42,1mm for a tension of approx. 250 daN

Maximum tension in use: 350 daN

Supplied with dimensions template for marking out + catch plate

FEATURES:

- Finish: Zinc Plated
- Material: Steel

- Dimensions: 111 x 49 x 10,5 mm
- Height: 111 mm
- Width: 49 mm
- Depth: 10,5 mm



