


Product data sheet

Characteristics

XZCC43FCP40B

female, DIN 43650 A, 4-pin, elbowed connector
- cable gland Pg 11

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Commercial Status	Commercialised
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector
Electrical connection	Elbowed female connector DIN 43650 A, 4 pins
Status LED	Without
Cable connection	Screw terminal / wire size $\leq 0 \text{ in}^2$ (1.5 mm ²) / clamping capacity 0.28...0.39 in (7...10 mm)

Complementary

Cable gland type	Pg 11
Cable connector fixing	Locking screw
[Ue] rated operational voltage	250 V AC
[In] rated current	16 A
Enclosure material	Plastic
Insulating resistance	> 0.1 G Ω
Contact resistance	$\leq 4000 \mu\text{Ohm}$
Product weight	0.08 lb(US) (0.035 kg)

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-40...257 °F (-40...125 °C)

Ordering and shipping details

Category	22483 - MACHINE CABLES
Discount Schedule	DS3
GTIN	00785901169154
Nbr. of units in pkg.	1
Package weight(Lbs)	0.07
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	DE

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0726 - Schneider Electric declaration of conformity

Contractual warranty

Period	18 months
--------	-----------