


## Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
12	21	5	1,43	0,67	0,028	-	20000	0,0063	61801-2RS1



### Calculation factors

$k_r = 0,015$

$f_0 = 9,7$