

**MNX PC 200/75 HT**



Sample photo

**Order symbol:** PC 200/75 HT  
**Product nbr:** 6011926  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074021984  
**EI. number:**  
 Finland: 3421612  
 Electric No. 8212022551  
 Denmark:  
 Electric No. Italy: 7352123  
 Electric No. Sweden: 6011926

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

**Dimensions:** Length Width Height **Accessories:**

|              |      |     |     |
|--------------|------|-----|-----|
| <b>mm:</b>   | 255  | 180 | 75  |
| <b>inch:</b> | 10.0 | 7.1 | 3.0 |

|              |                            |
|--------------|----------------------------|
| MIN 15       | DIN-15 Mounting rail       |
| MIN 20       | DIN-15 Mounting rail       |
| MIV 15       | DIN-35 Mounting rail       |
| MIV 20       | DIN-35 Mounting rail       |
| FP A 200/180 | Front plate (Aluminium)    |
| HFP 180      | Front plate hinge series   |
| FP 22046     | Wall fastening lug (4 pcs) |

**Materials:**

|                               |                      |
|-------------------------------|----------------------|
| <b>Material:</b>              | Polycarbonate        |
| <b>Base colour:</b>           | RAL 7035 -light grey |
| <b>Cover screws material:</b> | Polyamide            |
| <b>Cover colour:</b>          | Smoked grey          |
| <b>Cover screws colour:</b>   | Black                |
| <b>Gasket material:</b>       | TPE                  |

**Rating:**

Ingress Protection (EN 60529): IP66/IP67  
 Impact Resistance (EN 62262): IK08  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 746C 5"  
 Glow Wire Test (IEC 695-2-1) °C: 960  
 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

**Temperatures:**

|                                     |                |
|-------------------------------------|----------------|
| <b>Temperature °C (short term):</b> | -40 ... 120 °C |
| <b>Temperature °C (continuous):</b> | -40 ... 80 °C  |
| <b>Temperature °F (short term):</b> | -40 ... 250 °F |
| <b>Temperature °F (continuous):</b> | -40 ... 175 °F |

**Accessories:**

MIV 200 Mounting plate (Galvanized steel)

**Certificates:**

SGS Fimko

