

44 - Metric open end wrenches




Standards:

NF ISO 10102, NF ISO 3318, NF ISO 1711-1, NF ISO 691, ISO 10102, ISO 3318, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691, DIN 3110

Description:

- Open end wrenches = the open ends are slimmer than a standard combination wrench for better thickness accessibility. Examples: brake calipers, hydraulic hose locknuts.
- Heads hinged at 15°.
- Metric sizes: 3.2 to 42 mm.
- Presentation: satin chrome finish.

	A [mm]	Length L [mm]	Thickness E [mm]	Head Width B [mm]	Head Width B1 [mm]	Weight [Kg]
44.10X11	10x11	152.0	4.9	23.0	25	0.05
44.10X11PB	10x11	152.0	4.9	23.0	25.0	0.05
44.10X13	10x13	162.0	4.9	23.0	29	0.064
44.12X13	12x13	167.0	5.5	25.8	29.8	0.072
44.12X13PB	12x13	167.0	5.5	25.8	29.8	0.072
44.12X14	12x14	167.0	5.5	25.5	29.8	0.07
44.13X17		192.0	6.3	31.0	37	0.117
44.14X15	14x15	182.0	5.7	31.0	33.5	0.095
44.14X15PB	14x15	182.0	5.7	31.0	33.5	0.095
44.16X17	16x17	210.0	6.3	37.0	42	0.148
44.16X17PB	16x17	210.0	6.3	37.0	42.0	0.148
44.16X18	16x18	220.0	7.3	39.0	42	0.182
44.17X19		220.0	7.3	39.0	42	0.174
44.18X19	18x19	220.0	7.3	39.0	42	0.173
44.18X19PB	18x19	220.0	7.3	39.0	42.0	0.173
44.20X22	20x22	240.0	7.5	43.0	48.5	0.221
44.20X22PB	20x22	240.0	7.5	43.0	48.5	0.221
44.21X23	21x23	245.0	8.3	47.0	52	0.284
44.21X23PB	21x23	245.0	8.3	47.0	52.0	0.284
44.22X24	22x24	245.0	8.3	47.0	52	0.277
44.24X27	24x27	270.0	8.8	53.0	58	0.349
44.25X28		285.0	9.5	59.5	64	0.412
44.26X28	26x28	285.0	9.5	59.5	64	0.409
44.27X29	27x29	285.0	9.5	59.5	64	0.4
44.27X30	27x30	285.0	9.5	59.5	64	0.403
44.3.2X5.5	3.2x5.5	90.0	3.5	11.0	13.5	0.013
44.30X32	30x32	318.0	9.8	64.0	70	0.516

44.34X36	34x36	342.0	11.7	71.0	75	0.781
44.36X41	36x41	381.0	12.3	78.0	87	1.034
44.38X42	38x42	381.0	12.3	78.0	87	1.022
44.4X5	4x5	90.0	3.5	11.0	13.5	0.01
44.6X7	6x7	120.0	3.7	15.0	17.5	0.02
44.6X7PB	6x7	120.0	3.7	15.0	17.5	0.02
44.8X10	8x10	137.0	4.2	19.0	22	0.033
44.8X9	8x9	137.0	4.2	19.0	22	0.035
44.8X9PB	8x9	137.0	4.2	19.0	22.0	0.035