


SPECIFICATION OF SURFACE MOUNT TYPE

1. Type	DSX321G
2. Frequency	26 MHz
3. Loading Capacitance	10 pF
4. Drive Level	10 uW +/- 2 uW (200 uW Max.)
5. Frequency Tolerance	+/- 10 ppm at 25 deg.C +/- 3 deg.C
6. Equivalent Series Resistance	40 ohm Max. / CL=Series
7. Temperature Drift	+/- 10 ppm / - 20 deg.C to + 85 deg.C
8. Operating Temp. Range	- 20 deg.C to + 85 deg.C
9. Storage Temp. Range	- 40 deg.C to + 90 deg.C
10. Shunt Capacitance	2.0 pF (Max.)
11. Insulation Resistance	500 Mohm Min. at 100 v DC
12. Aging	+/- 1 ppm Max. / year
13. Mode of Oscillation	AT - cut, Fundamental
14. Dimensions	Refer to Fig-1



KDS : manufacturer's code

Remarks

(1) Logo and Manufacturing Location

D : Japan

D : Indonesia

(2) Freq. 26

(3) Lot No.

Fig-1

DAISHINKU CORPORATION