


**solenoid coil**  
**VACF-B-B2-1**  
 Part number: 8030802



**Data sheet**

<b>Feature</b>	<b>Value</b>
Assembly position	Any
Duty cycle	100%
Insulation class	H
Characteristic coil data	24 V DC: 3.3 W
Permissible voltage fluctuation	+/- 10 %
Certificate issuing department	DNVGL-TAA000011J
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-20 ... 50 °C
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Maritime classification	see certificate
Authorisation	c UL us - Recognized (OL)
Electrical connection	To industry standard (11 mm) Plug pattern type B to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper