


# solenoid coil VACF-A-A1-1

Part number: 8030822

★ Core product range

FESTO



## Data sheet

Feature	Value
Assembly position	Any
Duty cycle	100%
Insulation class	H
Characteristic coil data	24 V DC: 2.6 W
Permissible voltage fluctuation	+/- 10 %
Certificate issuing department	DNVGL-TAA000011J
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Protection class	IP65
Ambient temperature	-20 ... 50 °C
Maritime classification	see certificate
Authorisation	c UL us - Recognized (OL)
Electrical connection	to EN 175301-803 Plug pattern type A to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper