

plastic tubing PUN-H-10X1,5-TBL

Part number: 8048701

★ Core product range

Approved for use in food processing (hydrolysis resistant)

This product is not suitable for CN and PK push-in fittings.

FESTO



Data sheet

| Feature | Value |
|--|---|
| Outside diameter | 10 mm |
| Bending radius relevant for flow rate | 52 mm |
| Inside diameter | 7 mm |
| Min. bending radius | 28 mm |
| Tubing characteristics | Suitable for energy chains in applications with high cycle rates |
| Tubing test conditions | Suitable for energy chains: > 5 million cycles to FN 942021 |
| Temperature dependent operating pressure | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| Ambient temperature | -35 ... 60 °C |
| Product weight according to length | 0.0465 kg/m |
| Pneumatic connection | For push-in connector outside diameter 10 mm |
| Colour | Translucent blue |
| Shore hardness | D 52 +/-3 |
| Materials note | Free of copper and PTFE Conforms to RoHS |
| Material tubing | TPE-U(PU) |