


# Ribbon Cable, PVC



## Specification

Conductor Material	Stranded bare copper
Conductor Size	14/0.15AS±0.008mm*8PCS
Min. Average Thickness	0.37mm±0.05mm
Insulation Material	45P PVC
Pitch	1.4mm
Outer Diameter	1.4mm±0.05mm*11.2mm±0.4mm
Temperature	80°C
Colour	Brown, Red, Orange, Yellow, Green, Blue, Purple, Grey
Roll	30M/Roll
Operating Temperature Min.	-15 °C
Voltage rating	300 V
Fire behaviour	UL 94 V2



**Art. Nr.**  
**RND 475-00811**