


Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description	Date	Approved		
Technology	Piezo		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS <div style="text-align: center;">  DB UNLIMITED </div>	1	Released from Engineering	10/21/2013	J.S		
Resonant Frequency	3100	(Hz)							
Rated Voltage	12	(V)							
SPL @ 10cm	125	(dBA)							
Tone	Siren								
Mount Type	Flange Mount								
Voltage Range	9 ~ 15	(V)							
Max Rated Current	120	(mA)							
Housing Material	ABS								
Operating Temperature	-20 ~ +60	°C							
Storage Temperature	-20 ~ +60	°C							
Weight	90	(g)							
				Drawn by	Date	Checked by	Date	Approved by	Date
				A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
				Piezo Indicator			IP1072612-1		