

## Coaxial Cable Connector 16\_QMA-50-3-1/133\_N

### Description

Right angle cable plug

Interface standards  
QMA QLF compliant



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 18 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact crimped  
Weight 0.0081 kg

#### Environmental Data

Operating temperature -40 °C to 85 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing DOU-00005830  
Catalogue drawing DOU-00005832  
Assembly instruction DOC-0000178735

### Ordering Information

Bulk 100 pcs package 16\_QMA-50-3-1/133\_NH  
Single package 16\_QMA-50-3-1/133\_NE

### Additional Information

Suitable cables RG\_400\_/U, RG\_223\_/U, ENVIROFLEX\_400, RADOX\_RF\_400, ENVIROFLEX\_142, RADOX\_RF\_142