



Fuse holder, low voltage, 32 A, AC 690 V, 10 x 38 mm, 3P, UL, IEC

Referencia 3Pole 30A 600V MFH For 10X38 Midget fuse
Catalog No. CHM3DU

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	32
Rated voltage			AC 690 V
Size			10 x 38 mm
Description			DIN rail mounting colour-coded Rated for use with 75°C or 90°C wire fine stranded wire spade terminals and with comb-bus bars Use any higher temperature rated wire with appropriate derating. Modular
Number of poles			3P
usable for size/applications			for cylindrical fuse-links
Standard/Approval			UL IEC
Standards/Regulations			IEC cULus CCC CSA UR

Technical data ETIM 7.0

Aparatos de protección y fusibles (EG000020) / Soporte para fusible cilíndrico (EC002705)			
Tecnología electrónica, de automatización y de mando de procesos / Instalación eléctricas, equipo / Sistema de fusibles / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Tensión nominal		Volt	690
Método de montaje			Raíl DIN
Para tamaño de fusible			10 x 38 mm
Número de polos			3
Conmutación simultánea N-neutral			No
Bloqueable			Sí
Indicación de fallo óptico			No
Anchura según espacios de módulos			3
Profundidad		Millimeter	45.1
Grado de protección (IP)			Otros