

Item no.: 2002-2204
Product description: Double deck terminal block through/through n/n without marker
carrier housing color: blue suitable for Ex e applications
suitable for Ex i applications



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Current intensity EN	28 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Number of levels	2
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.25 - 4 mm ²
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	10.119 g
Color	blue
Wiring type	Front-entry

No. of connection Points	4
No. of potentials	2
Height	52 mm
Height	2.047 in
Width	5.2 mm



Width	0.205 in
Depth	70 mm
Depth	2.76 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-2204	CSA	154112-1536069	600	20	22-12
2002-2204	PTB	IECEXPTB03.0004U	440	20	0,2-4
2002-2204	PTB	PTB03Atex1162U	440	20	0,2-4
2002-2204	RosTest	8189158	440	20	0,2-4
2002-2204	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected