

In-Line Fuseholders



HR and HM Series In-Line Fuseholders for SFE and 1/4" x Various Length Fuses

Voltage Rating: 32V, 20A
No agency listings.


Electrical Ratings

Catalog Symbol	Includes Fuse	Wire
HRJ*	SFE-20	19" of #14
HRI	SFE-14	
HRH	SFE-9	
HRE	SFE-7 1/2	
HRG	SFE-6	
HRF	SFE-4	
HMJ**	SFE-20	8" of #14
HMI	SFE-14	
HMH	SFE-9	
HME	SFE-7 1/2	
HMG	SFE-6	
HMF	SFE-4	

*Also available as in-line fuseholder only with lead wire contacts, HRJ-LES-Fuse.
**Also available as in-line fuseholder only with lead wire contacts, HMJ-LES-Fuse.

- HHJ-A For 1/4" x 1 1/2" fuse, no wire or fuse included, accepts #18 - #22 wire.
- HHJ-B For 1/4" x 1 1/2" fuse, no wire or fuse included, accepts #12 - #16 wire.
- HHI-B For 1/4" x 1 1/2" fuse, no wire or fuse included, accepts #12 - #16 wire.

Dimensional Data



Data Sheet: 2122



HFA Series In-Line Waterproof Fuseholders for 1/4" x 1 1/4" Fuses

Construction:
Body - Phenolic;
Contacts - Copper crimp leads

Voltage Rating: 250V, 20A


Agency Information:
UL Recognized, (Guide IZLT2, File E14853)
UL Flammability Rating: 94VO

Electrical Ratings

Catalog Symbol	Amps	Volts	Terminals
HFA	20	250	Crimp #12 - #16
HFA-HH*	20	250	1/4" Q.C.

*No UL Recognition.

Dimensional Data



CE logo denotes compliance with European Union Low Voltage Directive (50-1000Vac, 75-1500Vdc). Refer to Data Sheet: 8002 or contact Bussmann Application Engineering at 636-527-1270 for more information.

Data Sheet: 2115




HHT Series In-Line Fuseholders for 5 x 15mm or 5 x 20mm Fuses

Construction:
Body - Black Thermoplastic
Contacts - Brass
Wire - 16 awg, red

Electrical Ratings

	Amps	Volts
5 x 15mm	5	32
5 x 20mm	10	32

Dimensional Data



Data Sheet: 2138

