

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300700022](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower D-Size (1 3/8"-M35) Field Attachable 3-Pole, Straight

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Field Attachable / Accessories
 Series [130070](#)
 Application Power
 Approvals UL Listed: E258922
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower D-Size
 Type Field Attachable Connector
 UPC 78678804602

Physical

Cable Diameter 11.00-21.00mm (.43-.82")
 Coupling Type External Thread
 Diagnostics / LEDs No
 Diagnostics Port No
 Gender Male
 Keyway Single
 Material - Connector Body Nylon
 Material - Coupling Nut Anodized Aluminum
 Material - Plating Mating Gold
 Net Weight 128.010/g
 Orientation Straight
 Poles 3
 Temperature Range - Operating -20°C to +90°C
 Wire Size AWG 10, 12, 14, 8

Electrical


Current - Maximum per Contact 32.0A
 Voltage - Maximum 600V AC/DC

Material Info

Engineering Number CA3006-39

Reference - Drawing Numbers

Sales Drawing SD-120336-003-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130070](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300700022](#)