

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300970264](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** Dust-Tight Strain Relief Wide Range Grip, 3/4" NPT, Straight Male, Cable Diameter 13.21-18.54mm (.520-.730"), Non-Insulated, Approximate Break Strength 136.08kg (300 lbs)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130097](#)  
 Eye Type N/A  
 Insulated No  
 NEMA Rating Dust Tight  
 O-Ring N/A  
 Overview [Strain-Relief Cord Grips](#)  
 Product Name Dust-Tight  
 Type Strain Relief Grip  
 UPC 78678834610  
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

**Physical**


Approximate Break Strength 136.08kg (300 lbs)  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 13.21-18.54mm (.520-.730")  
 Color - Grommet N/A  
 Gender Male  
 Material - Body Zinc Plated Steel  
 Material - Grip Galvanized Steel  
 Mesh Length N/A  
 Net Weight 458.000/g  
 Number of Holes N/A  
 Thread Size 3/4" NPT

**Material Info**

Engineering Number 36509

**Reference - Drawing Numbers**

Sales Drawing SD-130097-003-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(b)-II**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130097 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300970264](#)