

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151341401](#)
Status: **Active**
Overview: [PicoBlade Connector System](#)
Description: PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 100.00mm Length, 14 Circuits, Natural

Documents:

| | |
|--------------------------------|--|
| 3D Model | Datasheet (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| 3D Model (PDF) | |

General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 15134 |
| Application | Signal, Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | PicoBlade-to-PicoBlade |
| Overmolded | No |
| Overview | PicoBlade Connector System |
| Product Name | PicoBlade |
| Type | Discrete Wire Assembly |
| UPC | 191128412537 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 100.00mm |
| Circuits (Loaded) | 14 |
| Color - Resin | Natural |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Net Weight | 6.000/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.25mm |
| Plating min - Mating | 0.889µm |
| Plating min - Termination | 0.914µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 0.90mm |
| Wire Size AWG | 28 |
| Wire/Cable Type | UL 1061 |


Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 125V |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2012343242-000 |
|---------------|----------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15134 Series](#)

Mates With

PicoBlade Header [53261](#) , [53047](#) , [53398](#) ,
[53048](#) . PicoBlade Plug Housing [51047](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15134-1401](#)