






© COPYRIGHT 1964 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS COVERED BY U. S. AND FOREIGN PATENTS AND /OR PATENTS PENDING.

REVISIONS				
LTR	DESCRIPTION	DATE	APPROVED	P.F.
U	OBSOLETE -7 PER CM-862	9-2-81	IB	RS
V	OBSOLETE -2 PER CM 2708	1-11-92	IB	RS



△ NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA AND WIRE BARREL.



△ NICKEL ON ENTIRE TERMINAL WITH .000030 GOLD OVER INSIDE OF MATING AREA.

GOLD	△ 3	.012 PH. BRZ	60617-6
GOLD	△ 1	BRASS	-5
TIN		PH. BRZ	-4
TIN		.012 BRASS	60617-1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±

CONTRACT NO
DR *m. FEHER 11-16-79*

CHK *D.S. Heide 1/4 1980*

APPD *D. [Signature] 1-7-80*

WIRE RANGE
24-18 AWS
INSULATION DIA
.100 MAX



AMP INCORPORATED
Harrisburg, Pa.

NAME
SOCKET, LOOSE PIECE,
COMMERCIAL MATE-N-LOK

SIZE **A** CODE IDENT NO **00779** DRAWING NO **60617**

SCALE — SHEET —

MATERIAL
SEE TABLE

FINISH
SEE TABLE