

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1720641006](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: 5.70mm Pitch, Mega-Fit Right-Angle Header, 6 Circuits, 0.76µm Gold (Au) Plating, UL 94 V-0, Glow-Wire Capable, Tray

Documents:

3D Model (PDF)	Application Specification AS-76823-100-001 (PDF)
3D Model	Test Summary TS-76823-100-001 (PDF)
Drawing (PDF)	Test Summary TS-76825-001-001 (PDF)
Product Specification 1054171000-PS-000 (PDF)	Datasheet (PDF)
Product Specification 1720631000-PS-000 (PDF)	Symbol Footprint Data SYM-172064-1006-001 (PDF)
Product Specification PS-76823-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	172064
Application	Power, Wire-to-Board
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	887191558936

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.110/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm, 2.36mm
Packaging Type	Tray
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +120°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172064](#) Series

Mates With

Mega-Fit Receptacle Housings [171692](#)
, [170001](#) . Mega-Fit Overmolded Cable
Assembly [245136](#)

Termination Interface: Style Through Hole
Unmated Height 14.53mm

Electrical

Current - Maximum per Contact 23.5A
Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds) 030
Lead-freeProcess Capability SMC&WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Application Specification AS-76823-100-001
Product Specification 1054171000-PS-000, 1720631000-PS-000,
PS-76823-100-001
Sales Drawing SD-76825-0100-000
Symbol/Footprint Data SYM-172064-1006-001
Test Summary TS-76823-100-001, TS-76825-001-001

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172064-1006](#)