



P. C. B. LAYOUT

SPECIFICATIONS:

Current Rating: 2Amp
 Insulator Resistance: 1000Megohms min
 Dielectric withstanding: AC 500V
 Operating Temperature: -40° ~+105°
 Max Processing Temp: 230° for 30~60 seconds
 Contact Material: Phosphor Bronze
 Insulator Material: PA6T UL94V-0
 Plating: Gold Flash

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 220-2SMT-2*XP H=4.3MM					
DRAWN: LYF	DATE: 2008-04-29	CLIENT P/N		/			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-220-20012	REV.	A		