



P.C.B LAYOUT

Specification
 Insulator Material: Polyeser, UL94V-0
 Standard: PA6T
 Contact Material: Brass
 Contact plated: Gold Over Nickel

Poles: 2*7P (Double)
 Current Rating : 3Amp
 Contact Resistance: 20 Milliohms Max
 Insulation Resistance : 1000MΩ Min.
 Dielectric withstanding Voltage: AC 500V
 Operation Temperature : -40 °C -- +105 °C

核准:		日期:		深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD	
业务:		日期:			
制图:		日期:		品名规格: 210R-2*7P 双翅 弯排针 (3.0/6.7/11.1)	
leven		2018-06-12		客户料号 C2902696	
未注公差表 X.X ±0.2 X.XX ±0.10 X.XXX ±0.050		mm		比例 /	
		图纸编号: B-2100R14P-D010		版本 A	