


**RoHS  
Compliant  
Drawing For  
Reference Only**



規格 Specifications

額定負荷 Ratings	DC 30 V 0.5 A
絕緣電阻 Insulation Resistance	DC 250V 60 Sec. 100 m Ω Min
抗電強度 Dielectric Voltage	AC 500V (50~60Hz) 60 Sec.
操作力 Operating Force (Kgf)	插入力(Insertion Force) 0.3 ~ 2.0
	拔出力(Extraction Force) 0.3 ~ 2.0
負荷壽命 Operating Life With Load	5,000 次 Cycles

Model No.	DS-211A-SL	DS-211B-SL
Pin	Ø2.5	Ø2.0

6.	Cover	PC	1	Black
5.	Glued Paperboard	Phonetic	1	Yellow / Black
4.	Pin	Brass Strip	1	Ag Plated Over Ni Plated
3.	Terminal	Brass Strip	1	Ag Plated Over Ni Plated
2.	Contact Terminal	Sheet Iron	1	Ni Plated
1.	Pin Terminal	Brass Strip	1	Ag Plated Over Ni Plated

Tolerance Unless Otherwise Spec		
Within	1.5mm	±0.15
Over	1.5mm	±0.20

Technical requirement :  
 1. This product should meet EU RoHS related requirement.  
 2. The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.  
 3. The surface of metal part should be without any defect such as scour,nick,oxidation and plating problem.  
 4. The electronic performance should be the same as spec.

**DCI DRAGON CITY INDUSTRIES LIMITED**

Item Name	DC P[OWER JACK	Tolerance :
Item No.	DS-211-SL	Unit : mm

Design	K.W Law	Remark	Scale
Drawing	W.K Yeung	Remark	Material
Check	K.L Wong	Remark	Drawing No.
Approval	K.W Chan	Remark	Sheet

序 No	零件 Part	材料 Material	數量 Qty	備註 Remarks
------	---------	-------------	--------	------------

B003051632