

**NOTES:**

**MATERIAL**

1. Insulator Material: PBT+30%GF(UL94V-0)
2. Contact Material : Brass
3. Contact Plating :
  - AWP xx-7240-T : Gold flash over Ni
  - AWP xx-7540-T : Tin over Ni


**ELECTRICAL**

1. Current Rating : 3AMP
2. Withstand Voltage : 1000V AC/DC
3. Contact Resistance : 20mΩ max
4. Insulation Resistance: 1000MΩ min

**ENVIRONMENTAL**

1. Operation Temperature: -40°C to +105°C
2. Packing: Tray

- ④ 6P-8P Without Slot "M" and "N"
- 10P-12P With Slot "M" , Without Slot "N"
- 14P-64P With Slot "M" and "N"
- ⑥ Wire Spec: AWG28



Section A-A

**RoHS compliant**



File No.: E198287

⑤

Scale	Free	⑥	Add wire spec	14.02.2014	Amy		Date	Name	Customer-No.
TOLERANCE		⑤	Add the UL-File No	13.12.2013	Winnie	Drawn	25.01.2006	Alex	ASSMANN WSW-No. <b>AWP xx-7x40-T</b>
X.X	±0.40	④	Update	27.03.2013	Winnie	Approved	14.02.2014	Amy	
X.XX	±0.25	③	New p/n added	21.12.2009	Dean				
X.XXX	±0.15	②	Redraw	13.03.2009	Dean				Drawing-No.
Angle	±3°	①	Drawn	25.01.2006	Alex				<b>ASS 1194C CO</b> rev06
			Id.	Modification	Date	Name			Replace



**ASS 1194C CO** rev06

Replace

Sheet