



SMDC300F/24-2 Product Details

[Share](#) | [Print](#) | [Email](#)


SMDC300F/24-2 (RF3102-000)

TE Internal Number: RF3102-000

Active

PolySwitch Resettable Devices

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Surface Mount Application
- Vmax Operating = 24 V
- Vmax = 24 V
- Imax = 40 A
- Family Name = SMDC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

| | |
|---|---|
| <p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • SMDC300F/24 (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available | <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling |
|---|---|

[List all Documents](#)
[Feedback](#)

Product Features (Please use the Product Drawing for all design activity)

| | |
|--|--|
| <p>Product Type Features:</p> <ul style="list-style-type: none"> • Family Name = SMDC • CSA File Number = CA78165 <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Vmax Operating (V) = 24 • Vmax (V) = 24 • Imax (A) = 40 • IH (Room Temperature) (A) = 3 • IT (Room Temperature) (A) = 6.00 • Rmin (Ω) = 0.015 • R1 Max [Post Trip] (Ω) = 0.072 • Power Dissipation (Max) (W) = 1.7 <p>Termination Features:</p> <ul style="list-style-type: none"> • Construction = Surface Mount <p>Configuration Features:</p> <ul style="list-style-type: none"> • Form Factor (inches) = 2920 • Form Factor (mm) = 7555 | <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant • UL File Number = E74889 • TUV Certificate No. = R72130408 <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (Max.) (°C) = 85 <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Surface Mount <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Tape & Reel <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem |
|--|--|

