



preci-dip

## PCB CONNECTORS


**SERIES**  
**350**

**350-PP-1NN-01-899101**

Single row

2.54 mm, Surface mount perpendicular floating pin, Pin Ø 0.47 mm

Pin connectors, SMD.



### TECHNICAL SPECS.:

<b>Insulator</b>	Black glass filled polyester PCT-GF30-FR
<b>Flammability</b>	UL 94V-O
<b>Contact</b>	Brass CuZn36Pb3 (C36000)
<b>Connecting pin Ø</b>	0.47 mm
<b>Mechanical life</b>	Min. 500 cycles
<b>Rated current</b>	3 A
<b>Dielectric strength</b>	Min. 1000 V RMS
<b>Coplanarity SMD terminations</b>	Max. 0.1 mm (measured on 25 mm long connectors)

### ORDERING INFORMATION:

PP Plating code	Termination	Connecting pin
10	Gold 0.25 µm	Gold 0.25 µm
80	Tin	Tin

NN number of poles. Replace NN with the requested number of poles, e.g. 350-10-1NN-00-106101 for a single row version with 8 pins becomes 350-10-108-00-106101.

# TECHNICAL ASSISTANCE

## GENERAL SPECIFICATIONS:

The values listed below are general specs applying for PRECI-DIP socket and pin connectors. Please see individual catalog page for additional and product specific technical data.

Operating temperature range	-55 ... +125 °C
Climatic category (IEC)	55/125/21
Operating humidity range	annual mean 75 %
Max working voltage	100 VRMS/150 VDC (2.54 mm grid)

PRECI-DIP sockets are recognized by Underwriters Laboratories Inc. and listed under "Connectors for Use in Data, Signal, Control and Power Applications", File Nr. E174442

## MECHANICAL CHARACTERISTICS:

Clip retention	Min. 40 N (no displacement under axial force applied)
Contact (sleeve / clip) retention	Min. 3.3 N acc. to MIL-DTL-83734, pt 4.6.4.2

## ELECTRICAL CHARACTERISTICS:

Insulation resistance between any two adjacent contacts	Min. 10'000 M at 500 V AC
Capacitance between any two adjacent contacts	Max. 1 pF

### Air and creepage distances between any two adjacent contacts :

SERIES	3xx/4xx/7xx	80x	83x	85x	86x
mm	0.7	0.85 / 0.7	0.5	0.4 / 0.5	0.5

## ENVIRONMENTAL CHARACTERISTICS:

The sockets withstand the following environmental tests without mechanical and electrical defects:

- Dry heat steady state IEC 60512-11-9.11i / 60068-2-2.Bb: 125 °C, 16h
- Damp heat cyclic IEC 60512-11-12.11m / 60068-2-30.Db: 25/55 °C, 90 – 100 %rH, 1 cycle of 24 h
- Cold steady state IEC 60512-11-10.11j / 60068-2-1.A: -55 °C, 2 h
- Thermal shock IEC 60512-11-4.11d / 60068-2-14.Na: -55/125 °C, 5 cycles 30 min
- Sinusoidal vibrations IEC 60512-6-4.6d / 60068-2-6.Fc: 10 to 500 Hz, 10 g, 1 octave/min, 10 cycles for each axis
- Shock IEC 60512-6-3.6c / 60068-2-27.Ea: 50 g, 11 ms, 3 shocks in three axis

During the above two tests no contact interruption >50 ns does appear.

- Solderability J-STD-002A, Test A, 245°C, 5 s solder alloy SnAg3.8Cu0.7
- Resistance to soldering heat J-STD-0020C, 260°C, 20 s
- Moisture sensitivity J-STD-020C level 1
- Resistance to corrosion :
  - 1) Salt spray test IEC 60068-2-11.Ka: 48 h
  - 2) Sulfur dioxide (SO<sub>2</sub>) test IEC 60068-2-42 Kc: 96 h at 25 ppm SO<sub>2</sub>, 25 °C, 75 %rH
  - 3) Hydrogen sulfide (H<sub>2</sub>S) test IEC 60068-2-43 Kd: 96 h at 12 ppm H<sub>2</sub>S, 25 °C, 75 %rH

## SOLDERLESS COMPLIANT PRESS-FIT CHARACTERISTICS:

### PRESS-FIT CHARACTERISTICS MEASURED ACC. TO IEC 60352-5

- Press-in force: 90 N max. (at min. hole dia.) / 65 N typ.
- Push-out force: 30 N min. (at max. hole dia.) / 50 N typ.
- Push-out 3rd cycle: 20 N min. (at max. hole dia.)

## PCB HOLE DIMENSIONS

- 2 mm grid: Finished hole  $\varnothing$ :  $0.7 + 0.09/-0.06$  mm | Drilled hole  $\varnothing$ :  $0.8 \pm 0.02$  mm
- 2.54 mm grid: Finished hole  $\varnothing$ :  $1 + 0.09/-0.06$  mm | Drilled hole  $\varnothing$ :  $1.15 \pm 0.02$  mm

## PCB HOLE PLATING

- PCB surface finish: Hole plating
- Tin: 5-15  $\mu\text{m}$  tin over min. 25  $\mu\text{m}$  copper
- Copper: min. 25  $\mu\text{m}$  copper
- Gold over nickel: 0.05-0.2  $\mu\text{m}$  gold over 2.5-5  $\mu\text{m}$  nickel over min. 25  $\mu\text{m}$  copper

## PACKAGING:

Standard connector packaging is card box.

SMD mount connectors available on request with Tape & Reel packaging acc. to EIA Standard 481.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Preci-dip:

[350-80-128-01-899101](#) [350-80-139-01-899101](#) [350-80-138-01-899101](#) [350-80-137-01-899101](#) [350-80-136-01-899101](#) [350-80-135-01-899101](#) [350-10-111-01-899101](#) [350-10-110-01-899101](#) [350-10-109-01-899101](#) [350-10-108-01-899101](#) [350-10-107-01-899101](#) [350-10-119-01-899101](#) [350-10-130-01-899101](#) [350-10-116-01-899101](#) [350-10-115-01-899101](#) [350-10-114-01-899101](#) [350-10-113-01-899101](#) [350-10-112-01-899101](#) [350-10-123-01-899101](#) [350-10-122-01-899101](#) [350-10-121-01-899101](#) [350-10-120-01-899101](#) [350-10-104-01-899101](#) [350-10-118-01-899101](#) [350-80-116-01-899101](#) [350-10-128-01-899101](#) [350-10-127-01-899101](#) [350-10-126-01-899101](#) [350-10-125-01-899101](#) [350-10-124-01-899101](#) [350-10-103-01-899101](#) [350-10-102-01-899101](#) [350-10-105-01-899101](#) [350-10-106-01-899101](#) [350-10-117-01-899101](#) [350-10-160-01-899101](#) [350-10-159-01-899101](#) [350-10-158-01-899101](#) [350-10-157-01-899101](#) [350-10-129-01-899101](#) [350-80-105-01-899101](#) [350-10-155-01-899101](#) [350-80-102-01-899101](#) [350-10-164-01-899101](#) [350-10-163-01-899101](#) [350-10-162-01-899101](#) [350-10-161-01-899101](#) [350-80-109-01-899101](#) [350-80-108-01-899101](#) [350-80-107-01-899101](#) [350-80-106-01-899101](#) [350-10-154-01-899101](#) [350-80-104-01-899101](#) [350-80-103-01-899101](#) [350-80-114-01-899101](#) [350-80-113-01-899101](#) [350-80-112-01-899101](#) [350-80-111-01-899101](#) [350-80-110-01-899101](#) [350-10-136-01-899101](#) [350-10-135-01-899101](#) [350-10-134-01-899101](#) [350-10-133-01-899101](#) [350-10-132-01-899101](#) [350-10-144-01-899101](#) [350-10-156-01-899101](#) [350-10-141-01-899101](#) [350-10-140-01-899101](#) [350-10-139-01-899101](#) [350-10-138-01-899101](#) [350-10-137-01-899101](#) [350-10-149-01-899101](#) [350-10-148-01-899101](#) [350-10-147-01-899101](#) [350-10-146-01-899101](#) [350-10-145-01-899101](#) [350-10-143-01-899101](#) [350-80-117-01-899101](#) [350-10-142-01-899101](#) [350-10-153-01-899101](#) [350-10-152-01-899101](#) [350-10-151-01-899101](#) [350-10-150-01-899101](#) [350-80-146-01-899101](#) [350-80-145-01-899101](#) [350-80-144-01-899101](#) [350-80-143-01-899101](#) [350-80-154-01-899101](#) [350-80-115-01-899101](#) [350-80-141-01-899101](#) [350-80-151-01-899101](#) [350-80-150-01-899101](#) [350-80-149-01-899101](#) [350-80-148-01-899101](#) [350-80-147-01-899101](#) [350-80-158-01-899101](#) [350-80-157-01-899101](#) [350-80-156-01-899101](#) [350-80-155-01-899101](#) [350-80-140-01-899101](#)