

## PSZROX-0315 - PSZROX

### General Part Information

Product Description		PSZROX-0315
Article Number		33356
POPNut Type	<a href="#">i</a>	PSZROX
Standard Bulk Pack Quantity		10,000

### Geometry / Dimensions

Thread Size		M3
Body Type (open / closed)	<a href="#">i</a>	Open
Body Features	<a href="#">i</a>	Round
Body Length (mm)		9.00
Min. Grip Thickness (mm)		0.50
Max. Grip Thickness (mm)		1.50
Head Style	<a href="#">i</a>	Reduced Head
Hole Diameter (mm)		4.90
Head Diameter (mm)		5.30
Head Thickness (mm)		0.50
Barrel Diameter (mm)		4.70

### Material / Weight

Material	<a href="#">i</a>	Steel
Weight per thousand (kg)		0.6

